



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TWRSGF20W Gfci TWR Self Test Duplex 20A 125V WH *Eaton Wiring Devices*

Catalog Number	TWRSGF20W
Manufacturer	Eaton Wiring Devices
Description	Self-Test Duplex Receptacle, 20 A, 125 V, 2 Poles, 3 Wires, Back and Side Wired Connection, Screw Mount, White, Tamper Resistant, Weather Resistant, 0.41 LB
Weight per unit	0.4000 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20A
dimensions	2.0250 IN X 2.8770 IN X 4.6140 IN
media	Yes

### Descriptions

Description	GFCI TWR SELF TEST DUPLEX 20A 125V WH
extra long description	EWD TWRSGF20W GFCI TWR Self Test Du
Features	Tested to the highest standards to provide dependable, state-of-the-art protection suitable for residential, commercial, and industrial settings, Eaton's Ground Fault Circuit Interrupter (GFCI) receptacles are designed to recognize a ground fault in your wiring and immediately break the flow of electricity, thus protecting you from electrical shock. Additionally, they prevent resetting if, once tripped, the ground fault renders the device no longer functional. When combined with Eaton's Arc Fault Circuit I

### Manufacturer Information

GTIN	00032664743030
UPC	032664743030

### Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	GFCI receptacle

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	1
Package	5
Weight Per each	0.4



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /  
Institutional Buildings / Structures - Other

environmental conditions

Tamper and weather resistant

standard

cULus Listed