



MILBANK
ENERGY AT WORK

U4702-X-5T9-K3-K2-IL



Catalog Number	U4702-X-5T9-K3-K2-IL	Insulation	Glass Polyester
Marketing Product Description	5 Terminal Ringless Large Closing Plate Lever Bypass 5th Terminal 9 Oclock Position Single Connector 4-600kcmil Double Connector 6-350kcmil 7-16 In Knockouts Lock Provision	Mounting	Surface Mount
UPC	784572324237	Enclosure	G90 Galvanized Steel with Powder Coat Finish
Length (IN)	4.844	Jaw Quantity	5 Terminal
Width (IN)	15	Bypass Type	Lever Bypass
Height (IN)	28.25	Number of Meter Positions	1 Position
Brand Name	Milbank	Equipment Ground	Ground Lug
Type	Ringless Meter Socket	Hub Opening	Large Closing Plate
Application	Meter Socket	Line Side Wire Range	4 AWG - 600 kcmil or Two 1/0 AWG - 250 kcmil
Standard	UL Listed;Type 3R	Load Side Wire Range	Two 6 AWG - 350 kcmil
Voltage Rating	600 Volts Alternating Current	Barrel Lock Provision	7/16 Inch Knockout for Barrel Lock Provision
Amperage Rating	320 Continuous Ampere	Number Of Receptacles	0
Phase	1 Phase		
Frequency Rating	60 Hertz		
Size	4.844L x 15W x 28.25H		
Number Of Cutouts	0		
Cutout Size	No Main Breaker		
Cable Entry	Overhead or Underground		
Terminal	Single Mechanical		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.