



MILBANK
ENERGY AT WORK

U4908-O-11GR



Catalog Number	U4908-O-11GR	Insulation	Glass Polyester
Marketing Product Description	4 Terminal Ringless Plain Top 520GR 520GR Surface Mount	Mounting	Surface Mount
UPC	784572271951	Enclosure	G90 Galvanized Steel with Powder Coat Finish
Length (IN)	5.188	Jaw Quantity	4 Terminal
Width (IN)	9	Bypass Type	No Bypass
Height (IN)	25.938	Number of Meter Positions	Single Power Head
Brand Name	Milbank	Equipment Ground	Ground Bar
Type	Ringless Meter Socket	Hub Opening	Plain Top
Special Features	Two Single Pole 20 Ampere Breakers	Number Branch Circuits	4
Application	Temporary Power	Number Of Receptacles	2
Standard	UL Listed;Type 3R	Receptacle Configuration	Two NEMA 5-20 Ground Fault
Voltage Rating	Up to 240 Volts Alternating Current		
Amperage Rating	125 Continuous Ampere		
Phase	1 Phase		
Frequency Rating	60 Hertz		
Size	5.188L x 9W x 25.938H		
Number Of Cutouts	2		
Cutout Size	Two Single Pole 20 Ampere Breakers		
Cable Entry	Underground		
Terminal	Lay in		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.