




MILBANK
ENERGY AT WORK

U5101-XL-11GR



Catalog Number	U5101-XL-11GR	Insulation	Glass Polyester
Marketing Product Description	4 Terminal Ringless Small Closing Plate 520GR 520GR Surface Mount	Mounting	Surface Mount
UPC	784572275812	Enclosure	G90 Galvanized Steel with Powder Coat Finish
Length (IN)	5.188	Jaw Quantity	4 Terminal
Width (IN)	8.875	Bypass Type	No Bypass
Height (IN)	25	Number of Meter Positions	Single Power Head
Brand Name	Milbank	Equipment Ground	Ground Bar
Type	Ringless Meter Socket	Hub Opening	Small Closing Plate
Special Features	Two Single Pole 20 Ampere Breakers	Line Side Wire Range	6 AWG - 350 kcmil
Application	RV Power	Number Branch Circuits	4
Standard	UL Listed;Type 3R	Number Of Receptacles	2
Voltage Rating	Up to 240 Volts Alternating Current	Receptacle Configuration	Two NEMA 5-20 Ground Fault
Amperage Rating	125 Continuous Ampere		
Phase	1 Phase		
Frequency Rating	60 Hertz		
Size	5.188L x 8.875W x 25H		
Number Of Cutouts	2		
Cutout Size	Two Single Pole 20 Ampere Breakers		
Cable Entry	Overhead or Underground		
Terminal	Lay in		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.