



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## U51360200S 200A 120/240V 4CKT 4T RINGLESS Meter Pedestal

Milbank

Catalog Number	U51360200S
Manufacturer	Milbank
Description	Metered Single Pedestal, 1 Phase, 4 Circuits, Powder Coat, Horn Bypass Switch, 200 A, 120/240 V Ac, 10-1/4 In Overall Length, 10 In Overall Width, 80 In Overall Height, Pedestal, #6 Awg to 350 Kcmil (Line/Load Neutral);#14 to 1/0 Awg (Line/Load Ground);#14 to #6 Awg Load Ground) Wire Size, Galvanized Steel (Enclosure) Material, 82 LB
Weight per unit	82.0 (lbs/each)
Product Category	Metered Power Outlet Pedestals

### Features

amperage rating	200 Continuous Ampere
Bypass Type	Horn Bypass
Cable Entry	Underground
cutout size	One 200 Ampere Main Breaker
insulation	Glass Polyester
Phase	1 Phase

### Dimensions and Weight

Size	10.25L x 9.688W x 80H
------	-----------------------

### Descriptions

Also Known As...	Meter Box Meter Socket
Description	200A 120/240V 4CKT 4T RINGLESS METER PEDESTAL
extra long description	MILB U5136-O-200S 200A RL MTR DB PE

### Manufacturer Information

Brand	MILBANK
GTIN	00784572275904
UPC	784572275904

### Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
Type	Ringless Meter Socket

### Packaging

Carton	1
Weight Per each	82



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Enclosure	G90 Galvanized Steel with Powder Coat Finish
Frequency Rating	60 Hertz
Mounting	Pedestal
standard	UL Listed;Type 3R