



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UAG114 1-1/4" Ua Sealtite Conduit, Bonded UI 50' *Southwire Company*

Catalog Number	UAG114
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 1-1/4 In Trade Size, 1.63 to 1.66 In Conduit Outer Diameter, 1.38 to 1.41 In Conduit Inner Diameter, TITAN2(TM) UI Style, 50 FT Length, Jacket: Thermoplastic;Core: Steel, Hot Dip Galvanized, Gray, 8 In Bend Radius, -67 °F Operating Temperature, +176 °F Operating Temperature, 80 LB/100 FT
Weight per unit	0.8000 (lbs/each)
Product Category	Liquid Tight Conduit

Features

outside diameter	1645
------------------	------

Descriptions

Description	1-1/4" UA SEALTITE CONDUIT, BONDED UL 50'
extra long description	SWC 55093305 Titan2 Type UL Liquidt

Manufacturer Information

GTIN	00032886042386
UPC	032886042386

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	LTM-UL

Packaging

Carton	50
Weight Per each	0.8