



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## UAG2100 2" Ua Sealtite Conduit, Bonded UI 100' *Southwire Company*

Catalog Number	UAG2100
Manufacturer	Southwire Company
Description	UI Liquid-Tuff™ Liquidtight Conduit, Type LFMC, 6200 Series, Liquidtight Flexible Metal Conduit. Hot Dipped Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 2 Inch Diameter, 100 Foot Reel
Weight per unit	1.5 (lbs/each)
Product Category	Flexible Metallic Conduit

### Features

Inside Diameter	2.020/2.045
Material	Steel
outside diameter	2.340/2.375

### Material, Color, and Finish

Color	Gray
Finish	PVC
Jacket Material	PVC

### Dimensions and Weight

Length	100
--------	-----

### Descriptions

Description	2" UA SEALTITE CONDUIT, BONDED UL 100'
extra long description	AFC 6207-30-00 2" LT UL LT LFMC GR
Features	UL LIQUIDTUFF™ Liquidtight Flexible Steel Conduit designed for use as a raceway for power, control and communication cables in accordance with Article 350 of the National Electrical Code.
Long Description	UL LIQUID-TUFF™ Liquidtight Conduit, Type LFMC, 6200 Series, Liquidtight Flexible Metal Conduit. Hot Dipped Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 2 inch Diameter, 100 Foot Reel
Product Type	2" LT UI LT LFMC Gray 100' RL
Short Description	2" LT UL LT LFMC GRAY 100' RL
Special Features	UL bonded strip 3/8in - 1.25in for grounding. UL Liquidtight all sizes. Sunlight resistant. Flame retardant PVD jacket. Hot dipped zinc galvanized steel low carbon steel core.

### Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680148087
Manufacturers Part Number	6207-30-00
UPC	077680148087



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	Liquidtight Flexible Metal Conduit

## Trade Size

Trade Size	2
------------	---

## Packaging

Carton	100
Weight	1.46
Weight Per each	1.49

## Uses, Certifications, and Standards

Application	For Service Entrance Wiring Upto 6 FT
Temperature Rating	176