



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

UAG34 3/4" Ua Sealtite Conduit, Bonded UI 100'

Southwire Company

Catalog Number	UAG34
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 3/4 In Trade Size, 1.03 to 1.05 In Conduit Outer Diameter, 0.82 to 0.84 In Conduit Inner Diameter, TITAN2(TM) UI Style, 100 FT Length, Jacket: Thermoplastic;Core: Steel, Hot Dip Galvanized, Gray, 5 In Bend Radius, -67 °F Operating Temperature, +176 °F Operating Temperature, 38 LB/100 FT
Weight per unit	0.3800 (lbs/each)
Product Category	Liquid Tight Conduit

Features

outside diameter	1040
------------------	------

Descriptions

Description	3/4" UA SEALTITE CONDUIT, BONDED UL
extra long description	SWC 55082703 Titan2 Type UL Liquidt

Manufacturer Information

GTIN	00032886042324
UPC	032886042324

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	LTM-UL

Packaging

Carton	100
Weight Per each	0.38