



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UAG341000 3/4" Ua Sealrite Conduit, Bonded UI 1000' *Southwire Company*

Catalog Number	UAG341000
Manufacturer	Southwire Company
Description	Flexible Conduit, 3/4 In Trade Size, 1.03 to 1.05 In Conduit Outer Diameter, 0.82 to 0.84 In Conduit Inner Diameter, 1000 FT Length, Jack: PVC Material, Galvanized, Gray, 4.25 In Bend Radius, -80 °F, 60 °F (Wet), 70 °F (Oil), -30 °F (Low Temperature) Operating Temperature, 176 °F, 140 °F (Wet), 158 °F (Oil), -22 °F (Low Temperature) Operating Temperature, 49 LB/100 FT
Weight per unit	0.3800 (lbs/ft)
Product Category	Flexible Metallic Conduit

Features

Inside Diameter	0.820/0.840
outside diameter	1.030/1.050

Material, Color, and Finish

Jacket Material	PVC
-----------------	-----

Descriptions

Description	3/4" UA SEALTITE CONDUIT, BONDED UL 1000'
extra long description	AFC 6203-60-00 3/4" UL LT LFMC GRA
Features	UL LIQUIDTUFF™ Liquidtight Flexible Steel Conduit designed for use as a raceway for power, control and communication cables in accordance with Article 350 of the National Electrical Code.

Manufacturer Information

GTIN	00077680120090
UPC	077680120090

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	Liquidtight Flexible Metal Conduit

Packaging

Carton	1000
Weight Per foot	0.38

Uses, Certifications, and Standards

Temperature Rating	176
--------------------	-----