

# Specifications



Photo is representative

## Eaton UASTS61C224CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, Six-jaw, 1-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UASTS61C224CH
<b>UPC</b>	786685216386
<b>PRODUCT LENGTH/DEPTH</b>	4.359 in
<b>PRODUCT HEIGHT</b>	20 in
<b>PRODUCT WIDTH</b>	12 in
<b>PRODUCT WEIGHT</b>	15 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

## Product specifications

<b>TYPE</b>	Instrument rated socket
<b>AMPERAGE RATING</b>	20A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Six-jaw
<b>PHASE</b>	Single-phase
<b>ENCLOSURE MATERIAL</b>	Aluminum
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	3-5/16 in hub cover plate
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>ACCESSORIES</b>	Factory wired test switch
<b>NUMBER OF SOCKETS</b>	1

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - UASTS61C224CH](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative

## Eaton UASTS61C224CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, Six-jaw, 1-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UASTS61C224CH
<b>UPC</b>	786685216386
<b>PRODUCT LENGTH/DEPTH</b>	4.359 in
<b>PRODUCT HEIGHT</b>	20 in
<b>PRODUCT WIDTH</b>	12 in
<b>PRODUCT WEIGHT</b>	15 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

## Product specifications

<b>TYPE</b>	Instrument rated socket
<b>AMPERAGE RATING</b>	20A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Six-jaw
<b>PHASE</b>	Single-phase
<b>ENCLOSURE MATERIAL</b>	Aluminum
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	3-5/16 in hub cover plate
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>ACCESSORIES</b>	Factory wired test switch
<b>NUMBER OF SOCKETS</b>	1

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - UASTS61C224CH](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

