



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

UF143WG250 Uf-B 14/3WG Cable-250'

Southwire Company

Catalog Number	UF143WG250
Manufacturer	Southwire Company
Description	Uf Cable, Sunlight-Resistant Additional Information, Landscape Irrigation;Underground Application, Black, Copper Conductor Material, 14 Awg Conductor Size, PVC Insulation Material, 0.060 In Insulation Thickness, Made In Usa, +60 °C Maximum Operating Temperature, 3 - Conductors, 1 - Strands, 0.184 In Outside Diameter, Carton Package Type, Strand Solid/Strand, UI Listed, 600 V Voltage Rating, 26/1000 LB/FT Weight
Weight per unit	0.1000 (lbs/ft)
Product Category	Uf-NMCB-Ug-Nmwu

Features

media	Yes
-------	-----

Dimensions and Weight

Length	250
--------	-----

Descriptions

Also Known As...	220 Wire Non-Metallic Sheathed Cable Thermoplastic-Sheathed Cable
Description	UF-B 14/3WG CABLE-250'
extra long description	SWC 13057555 UFB 14/3 g 250C
similar brands	Romex®

Manufacturer Information

Brand	Copper
GTIN	00032886166501
Manufacturers Part Number	13057555
UPC	032886166501

Taxonomies, Classifications, and Categories

Category Description	ROMEX (RX)& UF CABLE
Type	UF-B

Availability

minimum qty	250
-------------	-----

Packaging

Carton	250
Weight Per foot	0.1