



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UNF305 1" Female Union *Crouse-Hinds*

Catalog Number	UNF305
Manufacturer	Crouse-Hinds
Description	Union, 1 In Trade Size, Unf Model, Straight, Electro Galvanized With Chromate Treatment, Female Connection, 2 In Length, 1-7/8 In Diameter, 0.77 LB
Weight per unit	0.7700 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Threaded
dimensions	2.0900 IN X 2.1900 IN X 2.1900 IN

Descriptions

Description	1" FEMALE UNION
extra long description	CRS-H UNF305 1 NPT FEMALE UNF UNION
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit

Manufacturer Information

Brand	Eaton
GTIN	00782274644103
UPC	782274644103

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Union

Packaging

Carton	1
Package	5
Weight Per each	0.77

Uses, Certifications, and Standards

Enclosure	Class I Div 1 2 Group B C D, Class II Div 1 Group E F G, Class II Div 2 Group F G, Class III
standard	UL 886, CSA C22.2