



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



URD4040204PCS 4/0-4/0-2/0-4 Urd Mobile Home Feeder Alu PCS

King Wire Inc.

| | |
|------------------|---|
| Catalog Number | URD4040204PCS |
| Manufacturer | King Wire Inc. |
| Description | Type MC Cable, Flame Retardant;Moisture Resistant;Sunlight Resistant Additional Information, Mobile Home Application, Aluminum Alloy Conductor Material, 4/0-4/0-2/0-4 Awg Conductor Size, 200 A Current Rating, Polyethylene (XLpe) Insulation Material, 80 Mil Insulation Thickness, Made In Usa, +90 °C Maximum Operating Temperature, 1.380 In Outside Diameter, Reel Package Type, Strand Solid/Strand, Directive 2002/95/Ec;Federal Specification A-A-59544;Nec Nfpa 70, 2011 Edition;Rohs Compliant;UI 44;UI 84 Standard |
| Weight per unit | 0.8080 (lbs/ft) |
| Product Category | Direct Burial Wire |

Descriptions

| | |
|-------------|--|
| Description | 4/0-4/0-2/0-4 URD MOBILE HOME FEEDER ALU PCS |
|-------------|--|

Manufacturer Information

| | |
|-------|----------|
| Brand | Aluminum |
|-------|----------|

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Direct Burial Wire |
|----------------------|--------------------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per foot | 0.808 |