

# Eaton URTRS101BE

Catalog Number: URTRS101BE

Eaton meter socket, 3 5/16 in hub opening, 125A, Overhead, Hub opening, #8-2/0 kcmil, Four-jaw, Single-phase, #8-2/0 kcmil, Sockets:1, Three-wire, Ring, 600V



## General specifications

### Product Name

Eaton meter socket

### Catalog Number

URTRS101BE

### UPC

786685217826

### Product Length/Depth

3.63 in

### Product Height

11 in

### Product Width

8.25 in

### Product Weight

7 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## defaultTaxonomyAttributeLabel

### Type

3 5/16 in hub opening

### Amperage Rating

125A

### Feed type

Overhead

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

TN : Knoxville Utility Board (KUB)

### Line

#8-2/0 kcmil

### Load

#8-2/0 kcmil

### Number of wires

Three-wire

### Hub type

Hub opening

### Security

Ring

### Voltage rating

600 V

### Number of sockets

1

## Resources

### Brochures

Single Meter Sockets

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - METER SOCKET URTRS101(X)E, UNRRSS101(X)E  
125AMP, 1 ø OH/UG, RINGTYPE

### Specifications and datasheets

Eaton Specification Sheet - URTRS101BE



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)