

Eaton UT4R1121BCH

Catalog Number: UT4R1121BCH

Eaton meter socket, Multi position commercial or resi service, 100A, Over/under, 3-5/16 inch hub open, #6-250 kcmil, Four-jaw, 1-ph, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications



Product Name

Eaton meter socket

Catalog Number

UT4R1121BCH

UPC

782116094639

Product Length/Depth

4.5 in

Product Height

14.13 in

Product Width

40.63 in

Product Weight

40 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Multiple position commercial or residential service

Amperage Rating

100A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

ME : Central Maine Power

ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)

SC : South Carolina Electric and Gas (SCE&G)

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

Line

#6-250 kcmil

Load

#8-2/0 AWG

Number of wires

Three-wire

Hub type

3-5/16 in hub opening

Security

Ringless

Voltage rating

600 V

Number of sockets

4

Resources

Specifications and datasheets

[Eaton Specification Sheet - UT4R1121BCH](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)