Specifications



Eaton UT4R1121BCH

Eaton meter socket, Multi position commercial or resi service, 100A, Over/under, 3-5/16 inch hub open, #6-250 kcmil, Four-jaw, 1-ph, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications	
PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UT4R1121BCH
UPC	782116094639
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	14.13 in
PRODUCT WIDTH	40.63 in
PRODUCT WEIGHT	40 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed





Product specifications	
ТУРЕ	Multiple position commercial or residential service
AMPERAGE RATING	100A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	ME: Central Maine Power ME: Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company) SC: South Carolina Electric and Gas (SCE&G) AR: Entergy LA: Entergy MS: Entergy TX: Entergy
LINE	#6-250 kcmil
LOAD	#8-2/0 AWG
NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub opening
SECURITY	Ringless
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	4

Resources	
CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UT4R1121BCH
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc Eaton House

Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

© 2025 Eaton. All Rights







