



Catalog No. UTH4330TMEP

Description: RESIDENTIAL 320 AMP OH/UG

UPC No 784567721775

Home > Single Socket Metering > Single Socket Metering

METER SOCKET-(1) 320A 600V G90 N3R 4-TERMINAL LARGE HUB OPNG LEVER BYP TOP/BOT FEED TRIPLEX GROUND

Descriptors

Category	Single Socket Metering
----------	------------------------

Specifications

Utility Approval	Central Maine Pwr Approved
Phase	1
Voltage	600
Amps	320
Hub Type	Large Hub Opening
# of Terminals	4
Lever Bypass	Yes
Horned Bypass	No
Socket Type	Ringless
Enclosure Type	N3R
Metal Type	G90 Steel
Overhead/ Underground Line Feed	Top/Bottom
Wire Range (Cu/Al)	Studs - (1) 600MCM or (2) 350MCM
Triplex Ground	Yes

Publications

Title	Publication No.	Publication Type
Outline Drawing for Part # UTH4330TMEP METER SOCKET-(1) 320A 600V G90 N3R 4-TERMINAL LARGE HUB OPNG LEVER BYP TOP/BOT FEED TRIPLEX GROUND	UTH4330TMEP	Drawings-Outline and Dimensional

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.