

Eaton V3LM2C/UNV1

Catalog Number: V3LM2C/UNV1

Eaton Crouse-Hinds series Vaporgard V2L LED, 0.24A, Cool white, AC drive, 50W HID or 150-200W incan equiv, 50/60 Hz, Without guard, Heat and impact resistant glass lens, 3000 lm, Copper-free alum, No mounting module, 120-277 Vac, 29W

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Vaporgard V2L LED light fixture	V3LM2C/UNV1
	UPC
	662276652118
Product Length/Depth	Product Height
4.5 in	2.55 in
Product Width	Product Weight
4.5 in	1.7 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 2

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Lumens

3000

Color temperature

Cool white

Mounting Method

No mounting module

Voltage rating

120-277 Vac

Drive type

AC

Frequency rating

50/60 Hz

Lens material

Heat and impact resistant glass

Wattage

29W

Amperage Rating

0.24 A

Material

Copper-free aluminum

Power factor

> 0.9

Guard

Without guard

Equivalent luminaire

50W HID or 150-200W incandescent

Resources

Brochures

[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds series Vaporgard V2L/V3L LED brochure](#)

Catalogs

[Crouse-Hinds series Vaporgard V2L/V3L LED catalog page](#)

Certification reports

Vaporgard V2L Hazardous Area LED Light Fixtures UL certification

Vaporgard V2L Hazardous Area LED Light Fixtures Canadian certification

Installation instructions

IF 1885 - Vaporgard V2L/V3L Driver Modules - AC Version

Specifications and datasheets

Eaton Specification Sheet - V3LM2C/UNV1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)