

# Eaton V48M28T37CUNV

Catalog Number: V48M28T37CUNV

General-Purpose Transformer, Dry Type Distribution, DT-3, Three-phase, PV: 480V, Taps: 1 at +5% FCAN, 2 at -5% FCBN, SV: 208Y/120V, 150°C, 37.5 kVA, Cu windings, Frame: 916AN



Photo is representative

## General specifications

### Product Name

Eaton Totally enclosed non-ventilated transformer

### Catalog Number

V48M28T37CUNV

### UPC

786680072178

### Product Length/Depth

23.42 in

### Product Height

32.02 in

### Product Width

28.22 in

### Product Weight

907 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

### Catalog Notes

Totally enclosed non-ventilated



Powering Business Worldwide

## Physical Attributes

### Coil material

Copper

### Design

DT-3

### Frame

916AN

### Tap size

1 at +5% FCAN, 2 at -5% FCBN

### Type

Dry Type Distribution Transformer

## Performance Ratings

### Frequency rating

60 Hz

### Kva Rating

37.5 kVA

### Phase

Three-phase

### Primary voltage

480 V

### Secondary Voltage

208Y/120 V

### Temperature rise

150 °C rise

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - V48M28T37CUNV](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)