



**Vaportight Lighting & Accessories**

**T&B Catalog Number:**

VGL-02  
04226952510  
Active

**UPC Number:**

**Status:**

**Description:**

200-Watt Glass Globe

**Features**

Fully threaded globes prevent cross threading assuring a tight seal.

**Application**

Low maintenance indoor/outdoor lighting where moisture, dirt, dust, corrosion and rough service are problems.

To light cold storage facilities, walkways, bridges, tunnels and security locations.

Used with colored globes as warning, caution or directional lights.

**General**

Globe Material	Lime Crystal Glass
Maximum Wattage	200

**Dimension Information**

Inner Diameter (inches)	31 3/16
A (inches)	4 3/8
B (inches)	8 3/8
C (inches)	4 5/16
D (inches)	1

**Packaging**

T&B Order Multiple	6
T&B Inner Pack	1
Package in Units	6
T&B Sold in UOM	Each
T&B Weight Per UOM	2 lbs. Each

**Application Support**

Product Overview	Available on Website
D-Pak Merchandising System	Available on Website
Industry Cross Reference	Available on Website


**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:  
E 51152



For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)



**Vaportight Lighting & Accessories**

**T&B Catalog Number:**

VGL-02  
04226952510  
Active

**UPC Number:**

**Status:**

**Description:**

200-Watt Glass Globe

**Features**

Fully threaded globes prevent cross threading assuring a tight seal.

**Application**

Low maintenance indoor/outdoor lighting where moisture, dirt, dust, corrosion and rough service are problems.

To light cold storage facilities, walkways, bridges, tunnels and security locations.

Used with colored globes as warning, caution or directional lights.

**General**

Globe Material	Lime Crystal Glass
Maximum Wattage	200

**Dimension Information**

Inner Diameter (inches)	31 3/16
A (inches)	4 3/8
B (inches)	8 3/8
C (inches)	4 5/16
D (inches)	1

**Packaging**

T&B Order Multiple	6
T&B Inner Pack	1
Package in Units	6
T&B Sold in UOM	Each
T&B Weight Per UOM	2 lbs. Each

**Application Support**

Product Overview	Available on Website
D-Pak Merchandising System	Available on Website
Industry Cross Reference	Available on Website


**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:  
E 51152



For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)