



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



VHB12NUNVL850CDU 87W Led Highbay 50K 12000LM Dim 120-277V Narrow *Cooper Lighting Solutions*

Catalog Number	VHB12NUNVL850CDU
Manufacturer	Cooper Lighting Solutions
Description	Led High Bay, 12, 000 Lumens, Standard, Narrow (Aisle), High Impact Polycarbonate Lens, Universal Voltage 120-277, 80 Cri, 5000K, 0-10V Dimming Driver, Unit Pack.
Weight per unit	11.4 (lbs/each)
Product Category	Led Highbay Lighting

Features

amperage rating	N/A
Lamp Type	LED
Voltage Rating	120-277V
Wattage	N/A

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	87W LED HIGHBAY 50K 12000LM DIM 120-277V NARROW
extra long description	CLS VHB-12-N-UNV-L850-CD-U VHB 120
Long Description	LED High Bay, 12,000 lumens, Standard, Narrow (aisle), High Impact Polycarbonate Lens, Universal Voltage 120-277, 80 CRI, 5000K, 0-10V Dimming Driver, Unit Pack.
Product Type	VHB 12000LM N Unv 5000K CD U
Special Features	Compact, lightweight design for ease of installation

Manufacturer Information

Brand	METALUX INDUSTRIAL
GTIN	00080083785926
Manufacturers Part Number	VHBLED-LD1-12-N-UNV-L850-CD1-U
UPC	080083785926

Taxonomies, Classifications, and Categories

Category Description	LED HIGHBAY, LOWBAY & INDUSTRIAL LIGHTING
Type	INDUSTRIAL

Packaging

Carton	1
Weight Per each	11.4

Uses, Certifications, and Standards

Application	lighting
Mounting	Suspension Mount
standard	DLC Certified;UL Listed;DLC Premium Certified;ISO Certified