



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

320 SW 28TH ST
72712-0000, AR Bentonville
Phone: 479-250-1930
Fax: 479-250-1931



VHB24WUNVL850CDU 174W Led Highbay 50K 24000LM Dim 120-277V Wide D *Cooper Lighting Solutions*

Catalog Number	VHB24WUNVL850CDU
Manufacturer	Cooper Lighting Solutions
Description	Value High Bay, 24K Lumen, Wide Dist, 120-277V, 5000K, Dim
Weight per unit	13.0 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.809 (at277V)
Ballast Type	N/A
Lamp Type	LED
Voltage Rating	120-277V

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	174W LED HIGHBAY 50K 24000LM DIM 120-277V WIDE D
extra long description	CLS VHB-24-W-UNV-L850-CD-U VHB 2400
Long Description	Value High Bay, 24K Lumen, Wide Dist, 120-277V, 5000K, Dim
Product Type	VHB 24000LM W Unv 5000K CD U
Special Features	Compact, lightweight design for ease of installation

Manufacturer Information

Brand	METALUX INDUSTRIAL
GTIN	00080083818365
Manufacturers Part Number	VHB-24-W-UNV-L850-CD-U
UPC	080083818365

Taxonomies, Classifications, and Categories

Category Description	LED HIGHBAY, LOWBAY & INDUSTRIAL LIGHTING
Type	INDUSTRIAL

Packaging

Carton	1
Weight Per each	13

Uses, Certifications, and Standards

Application	lighting
Mounting	Suspended
standard	UL/cUL Listed - Damp Location;RoHS Compliant