



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

500 Rapides Drive  
71457-0000, LA Natchitoches  
Phone: 318-352-7414  
Fax: 318-352-4100



## VHBLEDD118WUNV 134W Led Highbay 50K 18000LM Dim 120-277V Wide

Cooper Lighting Solutions

Catalog Number	VHBLEDD118WUNV
Manufacturer	Cooper Lighting Solutions
Description	Led High Bay, White Enamel, CRS;Aluminum, 120/277 V Ac, 0.36 A @ 277 V, 160 W, 60000 H Average Life, 19263 LM Brightness (Lumens), 3500 K;4000 K;5000 K, 85, Non Dimmable, Wide Beam Spread, Surface/Chain Mount, 18-27/32 In Length, 14-19/32 In Width, 3-13/16 In Height, 15 LB
Weight per unit	15.0 (lbs/each)
Product Category	Led Highbay Lighting

### Features

amperage rating	0.36 (at 277V)
Ballast Type	N/A
Lamp Type	LED

### Material, Color, and Finish

Style	(blank)
-------	---------

### Descriptions

Description	134W LED Highbay 50K 18000LM Dim 120-277V Wide
extra long description	CLS VHB-18-W-UNV-L850-CD-U VHB 1800

### Manufacturer Information

Brand	METALUX
GTIN	00080083785902
Manufacturers Part Number	VHB-18-W-UNV-L850-CD-U
UPC	080083785902

### Taxonomies, Classifications, and Categories

Category Description	LED Highbay, Lowbay & Industrial Lighting
Type	INDUSTRIAL

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	1
Weight Per each	15

### Uses, Certifications, and Standards

Mounting	High Bay
standard	cULus Listed - Damp Location;40 Degree C Ambient Temperature Rating;RoHS Compliant;LM79/LM80 Compliant;DLC Qualified