



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3440 Hwy 114 Suite 200
76177-0000, TX Fort Worth
Phone: 682-237-5470
Fax: 682-237-5471



WCOC Orn Twist-On Wire Conn

Nsi Industries

Catalog Number	WCOC
Manufacturer	Nsi Industries
Description	Twist-On Wire Connector, (1) #18 Awg;(1) #20 Awg Conductor Size, (4) #16 Awg;(1) #20 Awg Conductor Size, Insulated, Thermoplastic Insulation Material, Copper Conductor Material, Orange Insulation Color, +221 °F Operating Temperature, 0.197 In Overall Width, 0.866 In Overall Height, 600 V, 0.34 LB
Weight per unit	0.3400 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Thermoplastic
Voltage Rating	600 V
Warranty	1 YEAR
Wire Type	COPPER

Material, Color, and Finish

Color	Orange
Finish	Thermoplastic

Dimensions and Weight

Depth	.197
Height	.866

Descriptions

Description	ORN TWIST-ON WIRE CONN
extra long description	NSI WC-O-C Standard Orange Easy Twi

Manufacturer Information

GTIN	00662381361516
UPC	662381361516

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Standard Wire Connectors

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Weight Per each	0.34



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3440 Hwy 114 Suite 200
76177-0000, TX Fort Worth
Phone: 682-237-5470
Fax: 682-237-5471

Uses, Certifications, and Standards

Application	Splicing Wire
environmental conditions	105 C
standard	UL 486C