



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WCOC Orn Twist-On Wire Conn

Nsi Industries

| | |
|------------------|---|
| Catalog Number | WCOC |
| Manufacturer | Nsi Industries |
| Description | Twist-On Wire Connector, (1) #18 Awg;(1) #20 Awg Conductor Size, (4) #16 Awg;(1) #20 Awg Conductor Size, Insulated, Thermoplastic Insulation Material, Copper Conductor Material, Orange Insulation Color, +221 °F Operating Temperature, 0.197 In Overall Width, 0.866 In Overall Height, 600 V, 0.34 LB |
| Weight per unit | 0.3400 (lbs/each) |
| Product Category | Electrical Fixture Conn (Nuts |

Features

| | |
|----------------|---------------|
| Material | Thermoplastic |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Type | COPPER |

Material, Color, and Finish

| | |
|--------|---------------|
| Color | Orange |
| Finish | Thermoplastic |

Dimensions and Weight

| | |
|--------|------|
| Depth | .197 |
| Height | .866 |

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | ORN TWIST-ON WIRE CONN |
| extra long description | NSI WC-O-C Standard Orange Easy Twi |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00662381361516 |
| UPC | 662381361516 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | WIRE NUTS |
| Type | Standard Wire Connectors |

Availability

| | |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

Packaging

| | |
|-----------------|------|
| Carton | 100 |
| Weight Per each | 0.34 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---------------|
| Application | Splicing Wire |
| environmental conditions | 105 C |
| standard | UL 486C |