



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WF4AL019SWW590CR 4" Led Wafer 27K/3K/35K/4K/5K 700/900/1100LM *Lithonia Lighting*

| | |
|------------------|---|
| Catalog Number | WF4AL019SWW590CR |
| Manufacturer | Lithonia Lighting |
| Description | The 4IN Canless Wafer Downlight Has An Innovative, Slim Design That Installs Quickly and Easily Into As Little As 3IN Of Plenum Space Allowing For It to Fit Into Ceiling Spaces Where Most Traditional Recessed Housings Do Not. Wafers Install Directly Into Dry Wall Eliminating The Need For Recessed Housings. Once Installed, Our Wafer Provides An All-In-One Design Featuring Switchable White Color Temperature and Adjustable Lumen Output Technology. This Technology Gives The Ultimate In Flexibility, Providing Y |
| Weight per unit | 1.1 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-------------------------------|-----------------------|
| average life | 50,000 |
| dimnable | Yes |
| Hardware | Yes |
| Lamp Included | Yes |
| Lamp Type | LED - Dynamic |
| lumens | 1100 LM,700 LM,900 LM |
| Material | Aluminum |
| Maximum Operating Temperature | 25 |
| media | Yes |
| Number of Lamps | 1 |
| Power Source | Hardwired |
| Shape | Round |
| Voltage Rating | 120 |
| Warranty | 3 |
| Wattage | 14.5 |

Material, Color, and Finish

| | |
|-----------------------------|--|
| Color | White |
| color rendering index (cri) | 90 |
| color temperature | 2700 ,3000 ,3500 ,4000 ,5000 ,Variable |
| Finish | Matte |
| Lens Color | WHITE |
| Lens Material | Polycarbonate |
| Style | CONTEMPORARY |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Dimensions and Weight

| | |
|--------|------|
| Height | 1.25 |
| Length | 4.72 |
| Width | 4.72 |

Descriptions

| | |
|------------------------|---|
| Construction | Canless,New Construction,Remodel |
| Description | 4" LED WAFER 27K/3K/35K/4K/5K 700/900/1100LM |
| extra long description | LITH WF4 ALO19 SWW5 90CRI MW M6 4IN |
| Features | Design Select |
| Long Description | The 4in Canless Wafer Downlight has an innovative, slim design that installs quickly and easily into as little as 3in of plenum space allowing for it to fit into ceiling spaces where most traditional recessed housings do not. Wafers install directly into dry wall eliminating the need for recessed housings. Once installed, our Wafer provides an all-in-one design featuring switchable white color temperature and adjustable lumen output technology. This technology gives the ultimate in flexibility, providing y |
| Product Type | Downlight |

Manufacturer Information

| | |
|---------------------------|----------------------------|
| Brand | JUNO |
| GTIN | 00197589041057 |
| Manufacturers Part Number | WF4 ALO19 SWW5 90CRI MW M6 |
| UPC | 197589041057 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED ARCHITECTURAL & SPECIFICATION LIGHTING |
|----------------------|--|

Trade Size

| | |
|---------------|------|
| aperture size | 4 in |
|---------------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 6 |
| Weight | 0.94 |
| Weight Per each | 1.06 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Decorative,Hospitality,Residential,Retail,Shower |
| environmental conditions | Indoor,Outdoor |
| Mounting | Recessed |
| standard | CSAusCA Title 24,ENERGY STAR,FCC 47CFR Part 15 Consumer,JA8 |