



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WF4SWW590CRIMWM6 4" 9W Led Wafer 27K/3K/35K/4K/5K 650LM

Lithonia Lighting - Acuity

Catalog Number	WF4SWW590CRIMWM6
Manufacturer	Lithonia Lighting - Acuity
Description	The 4-Inch Juno® Wafer™ Led Downlights With Switchable White Provides High-Quality Light Output and Efficiency and Features A Switch For Easy Color Temperature Adjustment, While Eliminating The Need For Recessed Housings. The Innovative Switchable White Feature Incorporates A Switch On Each Fixture For Simple Color Temperature Adjustment. Too Warm or Too Cool? Simply Toggle The Integrated Switch to Your Desired Setting (3000K Factory Default) and You Are Done! Whatever Your Application, Luminaires With Swi
Weight per unit	1.5 (lbs/each)
Product Category	Lighting

Features

average life	50,000
dimensions	4.7 x 1.1 x 1.1
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	670 LM
Material	Polycarbonate
Maximum Operating Temperature	25
Power Source	Hardwired
Shape	Round
Voltage Rating	120
Warranty	3
Wattage	9

Material, Color, and Finish

Color	White
color rendering index (cri)	90
color temperature	2700 ,3000 ,3500 ,4000 ,5000 ,Variable
Finish	Matte
Lens Color	WHITE
Lens Material	Polycarbonate
Style	CONTEMPORARY



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Dimensions and Weight

Height	1.1
Length	4.7
Width	4.7

Descriptions

Construction	Canless,New Construction,Remodel
Description	4" 9W LED WAFER 27K/3K/35K/4K/5K 650LM
extra long description	LITH WF4 SWW5 90CRI MW M6 4IN wafer
Features	Contractor Select
Long Description	The 4-inch Juno® Wafer™ LED Downlights with Switchable White provides high-quality light output and efficiency and features a switch for easy color temperature adjustment, while eliminating the need for recessed housings. The innovative Switchable White feature incorporates a switch on each fixture for simple color temperature adjustment. Too warm or too cool? Simply toggle the integrated switch to your desired setting (3000K factory default) and you are done! Whatever your application, luminaires with Swi
Product Type	Downlight

Manufacturer Information

Brand	JUNO
GTIN	00194994243465
Manufacturers Part Number	WF4 SWW5 90CRI MW M6
UPC	194994243465

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Downlight

Trade Size

aperture size	4 in
---------------	------

Packaging

Carton	1
Package	6
Weight	1
Weight Per each	1.5

Uses, Certifications, and Standards

Application	Decorative,Hospitality,Residential,Retail,Shower
environmental conditions	Indoor,Outdoor
Mounting	Recessed
standard	CSAusCA Title 24,ENERGY STAR,FCC 47CFR Part 15 Consumer,JA8