

Wiha Insulated Screwdrivers with SoftFinish® Cushion Grip Handle

Insulation Test Standards:

Insulation according to EN/IEC 60900, ASTM F-1505-01, New VDE 0682/part 201, DIN 7437, NFPA70E & CSA

Responds to OSHA's use specification 29 CFR1910

Each tool individually tested to 10,000 volts and rated to 1000 Volt ac or 1500 Volt dc

SoftFinish® handle


solid molded core with soft outer cushion grip. 40% more torque than conventional handles

Insulation

Molded directly onto the blade for permanent bonding


Blade

CVM tool steel, hardened to average 58/60RC


 **1000V**



 **1000Volt**

WH3205 Slotted Screwdriver, With Wiha-SoftFinish® Handle
Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA,  up to 1000 Volt. Individually Tested.

Item No.	mm	Inch	Inch	mm	Inch	mm	Inch	lbs.	pkg.
WH32005	2.0	.078	5/64	60	3.0	164	6.5	.05	10
WH32010	2.5	.098	3/32	75	3.0	179	7.1	.06	10
WH32012	3.0	.118	1/8	100	4.0	204	8.0	.07	10
WH32015	3.5	.139	9/64	100	4.0	204	8.0	.07	10
WH32017	4.0	.157	5/32	100	4.0	211	8.3	.12	10
WH32023	4.5	.177	3/16	100	4.0	211	8.3	.12	10
WH32024	4.5	.177	3/16	125	5.0	236	9.3	.12	10
WH32027	4.5	.177	3/16	150	6.0	261	10.2	.14	10
WH32025	4.5	.177	3/16	175	7.0	286	11.2	.13	10
WH32028	4.5	.177	3/16	200	8.0	311	12.3	.15	10
WH32031	5.5	.216	7/32	125	5.0	243	9.5	.15	10
WH32026	5.5	.216	7/32	175	7.0	293	11.5	.21	10
WH32034	6.0	.236	15/64	150	6.0	268	10.6	.21	10
WH32039	6.5	.255	1/4	150	6.0	268	10.6	.21	10
WH32042	8.0	.315	5/16	175	7.0	299	11.8	.34	10
WH32045	10.0	.393	3/8	200	8.0	318	12.5	.39	10




 **1000Volt**

WH32090 4 Piece Slotted & Phillips Set


Item No.	mm	mm	mm	Size	mm	.76 lbs.
WH32090	Slotted	3.5	100	0.6	Phillips 1	80
	Slotted	4.5	125	1.0	Phillips 2	100



 **1000Volt**

WH3210 Phillips Screwdriver, With Wiha-SoftFinish® Handle
Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA,  up to 1000 Volt. Individually Tested. Blade high alloy CVM steel, hardened, black finish. Insulation molded directly onto blade. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
WH32100	0	60	2.4	164	6.5	.06	10
WH32101	1	80	3.0	191	7.5	.12	10
WH32102	2	100	4.0	218	8.6	.20	10
WH32103	3	150	6.0	268	10.6	.34	10
WH32104	4	200	8.0	318	12.5	.39	10



 **1000Volt**

WH32091 5 Piece Slotted & Phillips Set

Item No.	mm	mm	mm	Size	mm	lbs.
WH32091	Slotted	3.0	100	0.6	Phillips 1	80
	Slotted	4.5	125	1.0	Phillips 2	100
	Slotted	6.5	150	1.2		

 **1000Volt**

WH32092 6 Piece Slotted & Phillips Set

Item No.	mm	mm	mm	Size	mm	lbs.
WH32092	Slotted	3.5	100	0.6	Phillips 1	80
	Slotted	4.5	125	1.0	Phillips 2	100
	Slotted	6.5	150	1.2	Phillips 3	150