

Wall Light

43 Watt LED

Classic Series LED
TRADITIONAL HID REPLACEMENT

Glare Free



Design is Protected by U.S. Patent No. 9,482,395



WLM43LED

WATTS: 43

CCT: 4500K

CCT: 3000K

LUMENS: 4,350

LUMENS: 3,908

LPW: 107 CRI: 82

LPW: 96 CRI: 81

DIMMING: 10-100%

DIMMING: 10-100%

Ordering Information

CATALOG #	DESCRIPTION	VOLTS	COLOR TEMP
WLM43LED	43W LED Wall Light	120-277	4500K
WLM43LED3K	43W LED Wall Light	120-277	3000K

Options

ADD SUFFIX #	DESCRIPTION
PC	120V Photocontrol
PM	208-277V Photocontrol
EB	Emergency Back-Up
4	480V Driver

Note: Atlas uses only premium LED compatible photocontrols

Performance

- 95% Efficient Reflector Targets the Light
- Eliminates Glare & Offensive Light
- Less Wasted Light
- More Footcandles on the Ground
- Creates a Smooth & Uniform Light Pattern


Dimensions and Specifications

Overall Height: 9.02"


Depth: 7.85"

Overall Width: 14.2"

Weight: 9.2 lbs.



Recommended Mounting Height - 12-14 ft.



Mtg. Hgt.	FOOTCANDLES ON THE GROUND						Avg. FCs 450 SQ. FT.
	90°			45°			
	5'	10'	15'	5'	10'	15'	
12'	9.2	7.9	3.6	9.9	5.3	3.0	6.5
14'	8.0	4.4	3.0	7.6	6.1	3.7	5.5

200,000+ HOURS



*The majority of Atlas Lighting Products are assembled in USA facilities by an American Workforce utilizing both Domestic and Foreign components



Wall Light

43 Watt LED

Classic Series LED
TRADITIONAL HID REPLACEMENT

Glare Free



Design is Protected by U.S. Patent No. 9,482,395



WLM43LED

WATTS: 43

CCT: 4500K

CCT: 3000K

LUMENS: 4,350

LUMENS: 3,908

LPW: 107 CRI: 82

LPW: 96 CRI: 81

DIMMING: 10-100%

DIMMING: 10-100%

Ordering Information

CATALOG #	DESCRIPTION	VOLTS	COLOR TEMP
WLM43LED	43W LED Wall Light	120-277	4500K
WLM43LED3K	43W LED Wall Light	120-277	3000K

Options


ADD SUFFIX #	DESCRIPTION
PC	120V Photocontrol
PM	208-277V Photocontrol
EB	Emergency Back-Up
4	480V Driver

Note: Atlas uses only premium LED compatible photocontrols

Performance

- 95% Efficient Reflector Targets the Light
- Eliminates Glare & Offensive Light
- Less Wasted Light
- More Footcandles on the Ground
- Creates a Smooth & Uniform Light Pattern

Recommended Mounting Height - 12-14 ft.



Mtg. Hgt.	FOOTCANDLES ON THE GROUND						Avg. FCs 450 SQ. FT.
	90°			45°			
	5'	10'	15'	5'	10'	15'	
12'	9.2	7.9	3.6	9.9	5.3	3.0	6.5
14'	8.0	4.4	3.0	7.6	6.1	3.7	5.5


Dimensions and Specifications

Overall Height: 9.02"

Depth: 7.85"

Overall Width: 14.2"

Weight: 9.2 lbs.



200,000+ HOURS



*The majority of Atlas Lighting Products are assembled in USA facilities by an American Workforce utilizing both Domestic and Foreign components

