



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WP3450IV Cat 5E RJ45 T568 A/B Conn Iv (M20)

Pass & Seymour/Legrand

Catalog Number	WP3450IV
Manufacturer	Pass & Seymour/Legrand
Description	The Vertical Design Of This High Quality Insert Makes Punchdown Termination Easy. The Insert Is For Use In All Keystone Wall Plates and Is Available In Multiple Colors, As Well As Convenient Contractor Packs.
Weight per unit	0.0391 (lbs/each)
Product Category	Outlets, Jacks, & Plates

Features

connection	RJ45 Female
Current Rating	1.5 (@ 20 degrees C)
insulation	Electrical Insulation Resistance: 500 (@ 100 VDC)

Material, Color, and Finish

Color	Ivory
Finish	Molded plastic chemically etched with diamond core finish

Dimensions and Weight

Size	0.67 x 076 x 1.18 (17.02 x 19.30 x 29.97)
------	---

Descriptions

Description	CAT 5E RJ45 T568 A/B CONN IV (M20)
extra long description	OnQ WP3450IV CAT 5E RJ45 T568 A/B C
Long Description	The vertical design of this high quality insert makes punchdown termination easy. The insert is for use in all Keystone wall plates and is available in multiple colors, as well as convenient contractor packs.
Product Type	Cat 5E RJ45 T568 A/B CNCTR Iv (M20)
Special Features	Quick Connect, Cat 5e, RJ45, Keystone connector

Manufacturer Information

Brand	Legrand On-Q
GTIN	00804428024859
Manufacturers Part Number	WP3450-IV
UPC	804428024859

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	RJ45 Female Cat 5e Keystone Insert



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	20
Package	120
Weight Per each	0.0391

Uses, Certifications, and Standards

Application	Residential
environmental conditions	0 to 93 (relative humidity, non-condensing)
Mounting standard	Keystone opening CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0
Temperature Rating	14 to 140 F (-10 to 60 C)