



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WP3450LA Cat 5E RJ45 T568 A/B Conn La (M20)

Pass & Seymour/Legrand

Catalog Number	WP3450LA
Manufacturer	Pass & Seymour/Legrand
Description	Keystone Connector, Snap-In Connection, 5 Category Level, Light Almond, 1.28 In Length, 0.64 In Width, 0.87 In Height, +14 °F Operating Temperature, +140 °F Operating Temperature, 0.04 LB
Weight per unit	0.0391 (lbs/each)
Product Category	Outlets, Jacks, & Plates

Features

connection	RJ45 Female
Current Rating	1.5 (@ 20 degrees C)
insulation	Electrical Insulation Resistance: 500 (@ 100 VDC)

Material, Color, and Finish

Finish	Molded plastic chemically etched with diamond core finish
--------	---

Dimensions and Weight

Size	0.67 x 076 x 1.18 (17.02 x 19.30 x 29.97)
------	---

Descriptions

Description	CAT 5E RJ45 T568 A/B CONN LA (M20)
extra long description	OnQ WP3450LA CAT 5E RJ45 T568 A/B C

Manufacturer Information

Brand	Legrand On-Q
GTIN	00804428024866
Manufacturers Part Number	WP3450LA
UPC	804428024866

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	RJ45 Female Cat 5e Keystone Insert

Packaging

Carton	20
Package	120
Weight Per each	0.0391

Uses, Certifications, and Standards

Application	Residential
environmental conditions	0 to 93 (relative humidity, non-condensing)
Mounting	Keystone opening
standard	CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0
Temperature Rating	14 to 140 F (-10 to 60 C)