



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WP3451WH Cat 5E RJ45 Coupler - WH (M20)

*Pass & Seymour/Legrand*

Catalog Number	WP3451WH
Manufacturer	Pass & Seymour/Legrand
Description	The CAT5E RJ45 Keystone Coupler Couples Two High-Speed Network Cables. The Female to Female Coupler Meets The Eia/Tia 568A Category 5E Specifications.
Weight per unit	0.0321 (lbs/each)
Product Category	Outlets, Jacks, & Plates

### Features

connection	RJ45 Female
Current Rating	1.5 (@ 20 degrees C)
insulation	Electrical Insulation Resistance: 500 (@ 100 VDC)

### Material, Color, and Finish

Color	White
Finish	Molded plastic chemically etched with diamond core finish

### Dimensions and Weight

Size	0.75 x 0.57 x 1.2 (19.15 x 14.4 x 30.5)
------	---

### Descriptions

Description	CAT 5E RJ45 COUPLER - WH (M20)
extra long description	OnQ WP3451WH CAT 5E RJ45 COUPLER -
Long Description	The Cat5e RJ45 Keystone Coupler couples two high-speed network cables. The female to female coupler meets the EIA/TIA 568A Category 5e specifications.
Product Type	Cat 5E RJ45 Coupler - White (M20)
Special Features	Cat 5e Coupler, RJ45 Connector, Keystone Insert

### Manufacturer Information

Brand	LEGRAND-ON-Q
GTIN	00804428028796
Manufacturers Part Number	WP3451-WH
UPC	804428028796

### Taxonomies, Classifications, and Categories

Category Description	COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS
Type	RJ45 Female Cat 5e Coupler Keystone Insert

### Packaging

Carton	20
Package	120
Weight Per each	0.0321



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Residential
environmental conditions	0 to 93 (relative humidity, non-condensing)
Mounting	Keystone opening
standard	CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0