



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street
72209-0000, AR Little Rock
Phone: 501-565-1785
Fax: 501-565-0827



WP3460WH Cat 6 RJ45 T568 A/B Conn WH (M20)

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | WP3460WH |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Keystone Connector, Snap-In Connection, White, 1.28 In Length, 0.64 In Width, 0.87 In Height, 0.04 LB/Ea |
| Weight per unit | 0.0369 (lbs/each) |
| Product Category | Outlets, Jacks, & Plates |

Features

| | |
|----------------|----------------------|
| connection | RJ45 Female |
| Current Rating | 1.5 (@ 20 degrees C) |

Material, Color, and Finish

| | |
|------------------|--|
| Contact Material | Phosphor bronze alloy with 50 µin gold-plating over 100 µin nickel |
| Finish | Molded plastic chemically etched with diamond core finish |

Dimensions and Weight

| | |
|------|----------------------------------|
| Size | 063 x 0.87 x 1.26 (16 x 22 x 32) |
|------|----------------------------------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | CAT 6 RJ45 T568 A/B CONN WH (M20) |
| extra long description | OnQ WP3460WH CAT 6 RJ45 T568 A/B CN |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Legrand On-Q |
| GTIN | 00804428024361 |
| Manufacturers Part Number | WP3460WH |
| UPC | 804428024361 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
| Type | RJ45 Female Cat 6 Keystone Insert |

Packaging

| | |
|-----------------|--------|
| Carton | 20 |
| Package | 120 |
| Weight Per each | 0.0369 |

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Residential |
| environmental conditions | 0 to 93 (relative humidity, non-condensing) |
| Mounting | Keystone opening |
| standard | CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0 |