



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WP3475IV Cat 5E QC A/B Keystone Conn Iv (M10)

*Pass & Seymour/Legrand*

Catalog Number	WP3475IV
Manufacturer	Pass & Seymour/Legrand
Description	Keystone Insert, Structured Wiring Application, Ivory Color, 1 CT;10 PK Package Quantity, Easily Terminate All Four Pairs Using The Legrand Punch & Go Tool (AC3400);RJ45 Inserts Can Be Terminated With Any 110 Punchdown Tool Special Features, Eia/Tia 568A/B Standards Met, 0.04 LB Weight
Weight per unit	0.0417 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

connection	RJ45 Female
insulation	Electrical Insulation Resistance: 500 (@ 100 VDC)

### Material, Color, and Finish

Finish	Smooth plastic
--------	----------------

### Dimensions and Weight

Size	0.76 x 0.67 x 1.18 (19.30 x 16.9 x 30)
------	--

### Descriptions

Description	CAT 5E QC A/B KEYSTONE CONN IV (M10)
extra long description	OnQ WP3475IV CAT 5E QC A/B KEYSTONE

### Manufacturer Information

Brand	LEGRAND-ON-Q
GTIN	00804428036678
Manufacturers Part Number	WP3475-IV
UPC	804428036678

### Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	RJ45 Female Cat 5e Keystone Insert

### Packaging

Carton	10
Package	60
Weight Per each	0.0417



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Enclosure	Housing Material: High Impact Flame Retardant Plastic
environmental conditions	0 to 93 (relative humidity, non-condensing)
Mounting	Keystone opening
standard	CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0
Temperature Rating	14 to 140 F (-10 to 60 C)