

# Eaton WPMV7L-UNV1

Catalog Number: WPMV7L-UNV1

Eaton Crouse-Hinds series Champ WPMV LED wall pack, 0.21A, Cool white, Dimmable driver, 3/4" entry, 150-175W equiv, 50/60 Hz, Tempered glass lens, 7000 lm, 115 lm/W, Die cast alum, Yoke mt, 7x6 distribution, 120-277 Vac, 125-250 Vdc, 59W

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Champ WPMV LED wall pack light fixture	WPMV7L-UNV1
	UPC
	662276892910
Product Length/Depth	Product Height
9.16 in	12.76 in
Product Width	Product Weight
12.6 in	14 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4X

### Ingress protection (IP) ratings

IP66

## Product specifications

### Lamp type

LED

### Lumens

7000

### Lumens per watt

115

### Color temperature

Cool white

### Optical distribution

7x6

### Mounting Method

Yoke

### Voltage rating

120-277 Vac, 125-250 Vdc

### Frequency rating

50/60 Hz

### Lens material

Tempered glass

### Wattage

59 W

### Amperage Rating

0.21 A

### Power factor

> 0.90

### Dimming

Dimmable driver

### Entry size

3/4"

### Material

Die cast aluminum

### Equivalent luminaire

150-175W

## Resources

### 3D models

[SP3D Design Package - Champ Pro WPMV LED Industrial Wallpack Light Fixtures](#)

### Brochures

[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds series industrial LED lighting solutions](#)

[Crouse-Hinds series WPMV LED brochure](#)

### Catalogs

[Crouse-Hinds series Champ WPMV LED catalog page](#)

### Installation instructions

[IF 1893 - Champ-Pak WPMVL LED Wall Pack](#)

### Specifications and datasheets

[Eaton Specification Sheet - WPMV7L-UNV1](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)