



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WPS40 400W HPS Wal-Pak Borosilicate Glass Hinged/Removab

Cooper Lighting Solutions

Catalog Number	WPS40
Manufacturer	Cooper Lighting Solutions
Description	Wal-Pak 400W HPS Multi-Tap Borosilicate Glass Wall Mount, W/Lamp Bronze, Hinged Removable Door
Weight per unit	22.8 (lbs/each)
Product Category	Lighting

Features

amperage rating	1.444 (at 277V)
Ballast Type	Electronic Ballast
Lamp Included	Yes
Lamp Type	HIGH PRESSURE SODIUM
Material	Die-Cast Aluminum
Number of Lamps	1
Voltage Rating	120-277V
Wattage	400W

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	400W HPS WAL-PAK BOROSILICATE GLASS HINGED/REMOVAB
extra long description	CLS WPS40 400W HPS MT PRISM GLASS L
Long Description	Wal-Pak 400W HPS Multi-Tap Borosilicate Glass Wall Mount, w/Lamp Bronze, Hinged Removable Door
Product Type	400W HPS MT Prism Glass Lens LMP BRZ
Special Features	Rugged die-cast aluminum housing and door in bronze powder-coat paint

Manufacturer Information

Brand	Cooper Lumark
GTIN	00080083541232
Manufacturers Part Number	WPS40
UPC	080083541232

Taxonomies, Classifications, and Categories

Category Description	Outdoor HID Lighting
Type	WALL MOUNT

Packaging

Carton	1
Weight Per each	22.7999



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting	WALL MOUNT
standard	UL/cUL Listed - Wet Location;IP66 Rated;40 Degree C Ambient Temperature Rating;ARRA Compliant;Title 20 Compliant;EISA Compliant;LM79/LM80 Compliant;DLC Premium;BAA Compliant