



**L.H. Dottie Company**  
 6131 Garfield Avenue  
 Commerce, California 90040  
 Call: 323-725-1000 • Fax: 323-721-0000

**"Building a Better Brand"**

## Item # WR8212, (WR8212) Steel Drywall Screw

Coarse thread Bugle Head drywall screws (Wood Rockets) are self piercing and are used for drywall, particle board and wood. The coarse threads provide for a quicker installation.



## Product Specifications | Packaging Specifications

### Product Specifications

<b>UPC Code</b>	781002162094
<b>Category Number</b>	4260
<b>Price per Quantity</b>	100
<b>Style/Type</b>	Bugle Head
<b>Drive</b>	Phillips
<b>Material</b>	Steel
<b>Finish</b>	Yellow Zinc Plated
<b>Diameter</b>	8 in.
<b>Length</b>	2-1/2 in.

### Packaging Specifications

<b>Package Type</b>	IB432
<b>Unit Quantity</b>	100
<b>Master Quantity</b>	1000
<b>Unit (UM)</b>	C
<b>Package Length</b>	5.60 in.
<b>Package Width</b>	4.10 in.
<b>Package Height</b>	2.70 in.
<b>Package Weight</b>	1.1000 lb.
<b>United Nations Standard Products &amp; Services Code (UNSPSC)</b>	31161509



**L.H. Dottie Company**  
 6131 Garfield Avenue  
 Commerce, California 90040  
 Call: 323-725-1000 • Fax: 323-721-0000

**"Building a Better Brand"**

## Item # WR8212, (WR8212) Steel Drywall Screw

Coarse thread Bugle Head drywall screws (Wood Rockets) are self piercing and are used for drywall, particle board and wood. The coarse threads provide for a quicker installation.



## Product Specifications | Packaging Specifications

### Product Specifications

<b>UPC Code</b>	781002162094
<b>Category Number</b>	4260
<b>Price per Quantity</b>	100
<b>Style/Type</b>	Bugle Head
<b>Drive</b>	Phillips
<b>Material</b>	Steel
<b>Finish</b>	Yellow Zinc Plated
<b>Diameter</b>	8 in.
<b>Length</b>	2-1/2 in.

### Packaging Specifications

<b>Package Type</b>	IB432
<b>Unit Quantity</b>	100
<b>Master Quantity</b>	1000
<b>Unit (UM)</b>	C
<b>Package Length</b>	5.60 in.
<b>Package Width</b>	4.10 in.
<b>Package Height</b>	2.70 in.
<b>Package Weight</b>	1.1000 lb.
<b>United Nations Standard Products &amp; Services Code (UNSPSC)</b>	31161509