



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WT51B Wingtwist Wire Connector, WT51 Yellow, 500/Bag

*Ideal*

Catalog Number	WT51B
Manufacturer	Ideal
Description	Wing Twist Connector, (2) #18 Awg Conductor Size, (3) #12 Awg Conductor Size, Yellow Insulation Color, +221 °F Operating Temperature, 1 to 6 Conductors, 600 V Ac, 2.1 LB
Weight per unit	0.0040 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

Material	Flame-retardant Polypropelene
Voltage Rating	600

### Material, Color, and Finish

Color	Yellow
-------	--------

### Descriptions

Description	WINGTWIST WIRE CONNECTOR, WT51 YELLOW, 500/BAG
extra long description	IDEAL WT51-B WINGTWIST WT51 YELLOW,
Features	With a full line for virtually every wire size and combination, the WingTwist Wire Connector offers a great combination of performance and value. The contoured wing design of the WingTwist provides maximum torque for a variety of electrical applications while the copolymer shell and live-action spring expand for smooth, progressive tightening providing dependable connections. With a tough, flame-retardant shell that withstands environmental extremes, and a long, deep skirt to provide maximum dielectric prote

### Manufacturer Information

Brand	Buchanan
GTIN	00781789611013
UPC	781789611013

### Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
----------------------	-----------

### Availability

minimum qty	500
-------------	-----

### Packaging

Carton	500
Package	5000
Weight Per each	0.004



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS