


ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100 70507-0000, LA Lafayette Phone: 337-235-7681 Fax: 337-235-7725





WT52SK Wingtwist Wire Conn, WT52 Red, 25, 000/Barrel Ideal

Catalog Number	WT52SK
Manufacturer	Ideal
Description	Buchanan, Wire Connector, Wingtwist, Conductor Range: 18 - 10 Awg, 2/12 Awg Min, 5/12 Awg Max, Number Of Conductors: 2 to 6, Material: Flame-Retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: WT52
Weight per unit	0.0080 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts
Features	
Material	Flame-retardant Polypropelene
Voltage Rating	600
Material, Color, and Finish	
Color	Red



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100 70507-0000, LA Lafayette Phone: 337-235-7681 Fax: 337-235-7725

_	•		
I IAC	rrin	tin	nc
Des	ыю	เมษ	113

Description	WINGTWIST WIRE CONN, WT52 RED, 25,000/BARREL
extra long description	IDEAL WT52-SK WINGTWIST WT52 RED, 2
Features	With a full line for virtually every wire size and combination, the WingTwist Wire Connector offers a great combination of performance and value. The contoured wing design of the WingTwist provides maximum torque for a variety of electrical applications while the copolymer shell and live-action spring expand for smooth, progressive tightening providing dependable connections. With a tough, flame-retardant shell that withstands environmental extremes, and a long, deep skirt to provide maximum dielectric prote
Long Description	Buchanan, Wire Connector, WingTwist, Conductor Range: 18 - 10 AWG, 2/12 AWG Min, 5/12 AWG MAX, Number Of Conductors: 2 to 6, Material: Flame-retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WT52
Product Type	Wingtwist WT52 Red, 25K BRL
Special Features	1,000V Maximum In Fixtures And Signs; Deep, Wide-Throated Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection; Features: Five Color-Coded Models Cover Common Construction Wire Ranges; Fixed, Square-Wire Spring Threads Itself Creating Secure Pressure Grip; Green Model Designed For Ground Connections; Model Number: WT52; UL 486C Listed (WGR UL 467 Listed) And CSA C22.2 #188 Certified; Unique Contoured Wing Design Acts As Built-In Wrench Providing Maximum Torque With Minimum E
anufacturer Information	
Rrand	Ruchanan

Ma

Brand	Buchanan
GTIN	00781789967639
Manufacturers Part Number	WT52-SK
UPC	781789967639

Taxonomies, Classifications, and Categories

Category Description WIRE NUTS

Packaging

Carton	25000
Weight Per each	0.008

1811 N. University Suite 100 70507-0000, LA Lafayette Phone: 337-235-7681 Fax: 337-235-7725

Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221
	F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS