

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

427 Metro Park Drive 75071-0000, TX Mckinney Phone: 972-542-1196 Fax: 972-542-2279



WW7160R 3/4"X60' Org GP Vny Tape Nsi Industries

Catalog Number	WW7160R
Manufacturer	Nsi Industries
Description	Warriorwrap WW-716-or Orange Vinyl General Use Electrical Tape Is Strong Enough For Professional Environments and Gets The Job Done Right The First Time, Every Time. This Tape Is 7MIL Thick, 60FT Long and Has A Max Temperature Rating Of 176 Degrees. The Strong Adhesion Helps Stick to Uneven Surfaces and Keeps The Backing In Place. Top Breaking Strength and Elasticity Make Warriorwrap An Excellent Choice For Splicing, Insulating or Marking Wires.
Weight per unit	0.1900 (lbs/each)
Product Category	Markers & Marking Tapes
Features	
adhesion strength	16
Material	Vinyl
maximum voltage	600
Temperature Range	20° - 176°
Tensile Strength	15
Warranty	1 YEAR
Material, Color, and Finish Backing Material	Plasticized Polyvinyl Chloride (PVC)
Color	Orange
Dimensions and Weight	
Length	60
Size	Thickness - 7mil - Length-60' - Width 3/4"
Thickness	.007
Width	.75



standard

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

427 Metro Park Drive 75071-0000, TX Mckinney Phone: 972-542-1196 Fax: 972-542-2279

Descriptions	
Description	3/4"X60' ORG GP VNY TAPE
extra long description	NSI WW-716-OR Vinyl Electrical Tape
Features	Its Warrior Time. At NSI, we put our 45 years of experience in the electrical industry into WarriorWrap, electrical tape strong enough to rise to any challenge. For insulating, splicing or marking cables and wires on the jobsite, choose WarriorWrap, available in 12 colors and 3 grades of quality. That quality starts with strong adhesion to stick to uneven surfaces. But that's not allâ€″it also features the best breaking strength around and unmatched elasticity to hold tight in indoor residential or commer
Long Description	WarriorWrap WW-716-OR Orange Vinyl General Use Electrical Tape is strong enough for professional environments and gets the job done right the first time, every time. This tape is 7mil thick, 60ft long and has a max temperature rating of 176 degrees. The strong adhesion helps stick to uneven surfaces and keeps the backing in place. Top breaking strength and elasticity make WarriorWrap an excellent choice for splicing, insulating or marking wires.
Product Type	Vinyl Electrical Tape 7MIL .75" 60FT or
Special Features	Good Ahesion and Elasticity, All Weather Performance, Great Tensile Strength, Resistant Tto UV, Abrasion and Corrosion, Falme-Retardant.
Manufacturer Information	
Brand	NSi
GTIN	00662381367396
Manufacturers Part Number	WW-716-OR
UPC	662381367396
Taxonomies, Classifications, and Cate	
Category Description	TABE
Туре	GENERAL PURPOSE
Packaging	
Carton	1
Weight Per each	0.19
Uses, Certifications, and Standards	
Application	NSI

UL 510