



# WW-716

## GENERAL Vinyl Electrical Tape

### COLORS

- Brown
- Red
- Orange
- Yellow

- Green
- Blue
- Purple
- Gray
- White

### SPECIFICATIONS

Thickness	7 mil
Adhesion to steel	16 oz/in
Adhesion to backing	16 oz/in
Tensile strength	15 lb/in
Elongation	200%
Operating temperature	20°F - 176°F
Dielectric strength	1200 V/mil
Certification	UL/CSA

### APPLICATIONS

- Used for marking, identifying, and insulating up to 600V
- Used for wire harnessing
- Used for jacketing on high voltage splices

### KEY FEATURES

- Good adhesion and elasticity
- All weather performance
- Great tensile strength
- Resistant to UV, abrasion and corrosion
- Flame-retardant
- Nine industry colors for all applications

### DIMENSIONS

- Thickness: .007"
- Width: ¾"
- Length: 60'

### COMPOSITION

- Backing: Plasticized polyvinylchloride (PVC)
- Adhesive material: rubber-based

### APPLICABLE REGULATORY STANDARDS

- UL Listed; UL Standard 510
- CSA Certified; CSA Standard C22.2

### STORAGE CONDITIONS

Product should be stored in humidity-controlled, dry conditions between 50°F and 73°F (10°C and 23°C). Relative humidity should be less than 65%.



[www.warriorwrap.com](http://www.warriorwrap.com)



NSi Industries, LLC  
800.321.5847  
[www.nsiindustries.com](http://www.nsiindustries.com)



# WW-716

## GENERAL Vinyl Electrical Tape

### COLORS

- Brown
- Red
- Orange
- Yellow

- Green
- Blue
- Purple
- Gray
- White

### SPECIFICATIONS

Thickness	7 mil
Adhesion to steel	16 oz/in
Adhesion to backing	16 oz/in
Tensile strength	15 lb/in
Elongation	200%
Operating temperature	20°F - 176°F
Dielectric strength	1200 V/mil
Certification	UL/CSA

### APPLICATIONS

- Used for marking, identifying, and insulating up to 600V
- Used for wire harnessing
- Used for jacketing on high voltage splices

### KEY FEATURES

- Good adhesion and elasticity
- All weather performance
- Great tensile strength
- Resistant to UV, abrasion and corrosion
- Flame-retardant
- Nine industry colors for all applications

### DIMENSIONS

- Thickness: .007"
- Width: ¾"
- Length: 60'

### COMPOSITION

- Backing: Plasticized polyvinylchloride (PVC)
- Adhesive material: rubber-based

### APPLICABLE REGULATORY STANDARDS

- UL Listed; UL Standard 510
- CSA Certified; CSA Standard C22.2

### STORAGE CONDITIONS

Product should be stored in humidity-controlled, dry conditions between 50°F and 73°F (10°C and 23°C). Relative humidity should be less than 65%.



[www.warriorwrap.com](http://www.warriorwrap.com)



NSi Industries, LLC  
800.321.5847  
[www.nsiindustries.com](http://www.nsiindustries.com)