



# WW-732

# PREMIUM Vinyl Electrical Tape

## COLORS

- Brown
- Red
- Orange
- Yellow

- Green
- Blue
- Purple
- Gray
- White

## SPECIFICATIONS

Thickness	7 mil
Adhesion to steel	33.3 oz/in
Adhesion to backing	33.2 oz/in
Tensile strength	19 lb/in
Elongation	285%
Operating temperature	0°F - 221°F
Dielectric strength	1289 V/mil
Certification	UL/CSA

## APPLICATIONS

- Used for marking, identifying, and insulating up to 600V
- Used for wire harnessing
- Used for jacketing on high voltage splices

## KEY FEATURES

- Superior adhesion and elasticity
- Extreme weather performance
- Excellent tensile strength
- Highly resistant to UV, abrasion and corrosion
- Flame-retardant
- Nine industry colors for all applications

## DIMENSIONS

- Thickness: .007"
- Width: ¾"
- Length: 66'

## COMPOSITION

- Backing: Plasticized polyvinylchloride (PVC)
- Adhesive material: rubber-based

## APPLICABLE REGULATORY STANDARDS

- UL Listed; UL Standard 510
- CSA Certified; CSA Standard C22.2

## STORAGE CONDITIONS

Product should be stored in humidity-controlled, dry conditions between 50°F and 73°F (10°C and 23°C). Relative humidity should be less than 65%.



[www.warriorwrap.com](http://www.warriorwrap.com)



NSi Industries, LLC  
800.321.5847  
[www.nsiindustries.com](http://www.nsiindustries.com)



# WW-732

# PREMIUM Vinyl Electrical Tape

## COLORS

- Brown
- Red
- Orange
- Yellow

- Green
- Blue
- Purple
- Gray
- White

## SPECIFICATIONS

Thickness	7 mil
Adhesion to steel	33.3 oz/in
Adhesion to backing	33.2 oz/in
Tensile strength	19 lb/in
Elongation	285%
Operating temperature	0°F - 221°F
Dielectric strength	1289 V/mil
Certification	UL/CSA

## APPLICATIONS

- Used for marking, identifying, and insulating up to 600V
- Used for wire harnessing
- Used for jacketing on high voltage splices

## KEY FEATURES

- Superior adhesion and elasticity
- Extreme weather performance
- Excellent tensile strength
- Highly resistant to UV, abrasion and corrosion
- Flame-retardant
- Nine industry colors for all applications

## DIMENSIONS

- Thickness: .007"
- Width: ¾"
- Length: 66'

## COMPOSITION

- Backing: Plasticized polyvinylchloride (PVC)
- Adhesive material: rubber-based

## APPLICABLE REGULATORY STANDARDS

- UL Listed; UL Standard 510
- CSA Certified; CSA Standard C22.2

## STORAGE CONDITIONS

Product should be stored in humidity-controlled, dry conditions between 50°F and 73°F (10°C and 23°C). Relative humidity should be less than 65%.



[www.warriorwrap.com](http://www.warriorwrap.com)



NSi Industries, LLC  
800.321.5847  
[www.nsiindustries.com](http://www.nsiindustries.com)