



## Control Circuit Transformers

### T&B Catalog Number:

X4150PSF1

### UPC Number:

80432536747

### Status:

Active

### Description:

150 VA rating 4 terminal transformer with 6.25/1.30 output amps with a primary fuse block and a secondary fuse clip

### Features

Epoxy encapsulated coils up through 750VA

Epoxy resin impregnated coils 1 kVA to 5 kVA

Laminations of high quality silicon steel

Minimum core loss

Copper magnet wire providing the highest quality and efficient operation

Molded-in terminals

84 degree C rise, 130 degree C insulation system

IP 20 Touch safe covers available as an option

### Standards

UL File # E175311; CSA File #LR27533

### Application

Provides stepped down voltages for machine tool control devices and industrial control panels

### Dimension Information

H x W x D (inches) 4.53 x 3.74 x 4.65

H x W x D (mm) 115 x 95 x 118

### Specifications

Output Current (Amps) 6.25/1.30

### Packaging

Package in Units 1

T&B Sold in UOM Each

T&B Weight Per UOM 8.33 lbs. Each

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com



## Control Circuit Transformers

### T&B Catalog Number:

X4150PSF1

### UPC Number:

80432536747

### Status:

Active

### Description:

150 VA rating 4 terminal transformer with 6.25/1.30 output amps with a primary fuse block and a secondary fuse clip

### Features

Epoxy encapsulated coils up through 750VA

Epoxy resin impregnated coils 1 kVA to 5 kVA

Laminations of high quality silicon steel

Minimum core loss

Copper magnet wire providing the highest quality and efficient operation

Molded-in terminals

84 degree C rise, 130 degree C insulation system

IP 20 Touch safe covers available as an option

### Standards

UL File # E175311; CSA File #LR27533

### Application

Provides stepped down voltages for machine tool control devices and industrial control panels

### Dimension Information

H x W x D (inches) 4.53 x 3.74 x 4.65

H x W x D (mm) 115 x 95 x 118

### Specifications

Output Current (Amps) 6.25/1.30

### Packaging

Package in Units 1

T&B Sold in UOM Each

T&B Weight Per UOM 8.33 lbs. Each

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com