



Powering Business Worldwide

pe.eaton.com



## IDC Fuse Terminal Blocks

**XBQT25FBE**

**UPC:**782116926893

### Dimensions:

- **Height:** X
- **Length:** 3.25 IN
- **Width:** .24 IN

**Notes:**As disconnect terminal block, 400V, as fuse terminal blocks 250V.

### Warranties:

- 1 year

### Specifications:

- **Type:** IEC-XB Series
- **Amperage Rating:** 15A (UL), 6.30A connection
- **Voltage Rating:** UL 300V
- **Maximum Wire Size:** 14 AWG/1.5 mm<sup>2</sup>
- **Quantity:** 50
- **Wire Size:** #20-14 AWG
- **Color:** Black

### Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBQT25FBE](#)

### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)



## IDC Fuse Terminal Blocks

**XBQT25FBE**

**UPC:**782116926893

### Dimensions:

- **Height:** X
- **Length:** 3.25 IN
- **Width:** .24 IN

**Notes:**As disconnect terminal block, 400V, as fuse terminal blocks 250V.

### Warranties:

- 1 year

### Specifications:

- **Type:** IEC-XB Series
- **Amperage Rating:** 15A (UL), 6.30A connection
- **Voltage Rating:** UL 300V
- **Maximum Wire Size:** 14 AWG/1.5 mm<sup>2</sup>
- **Quantity:** 50
- **Wire Size:** #20-14 AWG
- **Color:** Black

### Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBQT25FBE](#)

### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data