

# Eaton XBUT25BK

Catalog Number: XBUT25BK

Eaton XB IEC terminal block, Screw connection single level-through-feed, Black, 12 AWG/2.5 mm<sup>2</sup> maximum wire



## General specifications

Product Name	Catalog Number
Eaton XB IEC terminal block	XBUT25BK
UPC	Product Length/Depth
786685231303	1.85 in
Product Height	Product Width
2.17 in	0.2 in
Product Weight	Warranty
0.02 lb	1 year
Certifications	
UL Listed	
CSA Certified	

## Product specifications

### Type

IEC-XB Series

### Amperage Rating

32A (IEC), 22A (EN), 28A (EN), 20A (UL)

### Voltage rating

IEC 800V, EN 700V, UL 600V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XBUT25BK](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton XBUT25BK

Catalog Number: XBUT25BK

Eaton XB IEC terminal block, Screw connection single level-through-feed, Black, 12 AWG/2.5 mm<sup>2</sup> maximum wire



## General specifications

Product Name	Catalog Number
Eaton XB IEC terminal block	XBUT25BK
UPC	Product Length/Depth
786685231303	1.85 in
Product Height	Product Width
2.17 in	0.2 in
Product Weight	Warranty
0.02 lb	1 year
Certifications	
UL Listed	
CSA Certified	

## Product specifications

### Type

IEC-XB Series

### Amperage Rating

32A (IEC), 22A (EN), 28A (EN), 20A (UL)

### Voltage rating

IEC 800V, EN 700V, UL 600V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - XBUT25BK](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)