

# Eaton XBUT25BU

Catalog Number: XBUT25BU

Eaton XB IEC terminal block, 5.2 mm Screw connection single level-through-feed, Blue, 12 AWG/2.5 mm<sup>2</sup> maximum wire, IEC 800V, EN 700V, UL 600V, IEC #26-12 AWG, EN #26-12 AWG, UL #26-12 AWG wire, IEC 32A, EN 22,28A, UL 20A



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XB IEC terminal block	XBUT25BU
<b>UPC</b>	<b>Product Length/Depth</b>
782116894277	1.85 in
<b>Product Height</b>	<b>Product Width</b>
2.17 in	0.2 in
<b>Product Weight</b>	<b>Warranty</b>
0.19 lb	1 year
<b>Certifications</b>	
UL Listed	
CSA Certified	

## defaultTaxonomyAttributeLabel

### Type

IEC-XB Series

### Amperage Rating

32A (IEC), 22A (EN), 28A (EN), 20A (UL)

### Voltage rating

IEC 800V, EN 700V, UL 600V

## Resources

### Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Drawings

[XBUT25 3D Inventor](#)

[XBUT25 AutoCAD 2D Footprint](#)

[XBUT25 2D PDF](#)

[XBUT25 AutoCAD 2D Footprint \(mm\)](#)

[XBUT25 3D Model Xchange](#)

[XBUT25 2D Drawing Xchange](#)

### Specifications and datasheets

[Eaton Specification Sheet - XBUT25BU](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)