

# Specifications



## Eaton XBUT4D22

Eaton XB IEC terminal block, Screw Connection Multi-Conductor Terminal Blocks, Gray, 10 AWG/4 mm<sup>2</sup> maximum wire, Four-wire

### Product specifications

<b>TYPE</b>	IEC-XB Series
<b>AMPERAGE RATING</b>	36A (IEC), 30A (UL)
<b>VOLTAGE RATING</b>	IEC 500V, UL 150V

### General specifications

<b>PRODUCT NAME</b>	Eaton XB IEC terminal block
<b>CATALOG NUMBER</b>	XBUT4D22
<b>UPC</b>	782116905188
<b>PRODUCT LENGTH/DEPTH</b>	1.85 in
<b>PRODUCT HEIGHT</b>	2.17 in
<b>PRODUCT WIDTH</b>	0.24 in
<b>PRODUCT WEIGHT</b>	0.04 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL Listed CSA Certified



Powering Business Worldwide

# Specifications



## Eaton XBUT4D22

Eaton XB IEC terminal block, Screw Connection Multi-Conductor Terminal Blocks, Gray, 10 AWG/4 mm<sup>2</sup> maximum wire, Four-wire

### Product specifications

<b>TYPE</b>	IEC-XB Series
<b>AMPERAGE RATING</b>	36A (IEC), 30A (UL)
<b>VOLTAGE RATING</b>	IEC 500V, UL 150V

### General specifications

<b>PRODUCT NAME</b>	Eaton XB IEC terminal block
<b>CATALOG NUMBER</b>	XBUT4D22
<b>UPC</b>	782116905188
<b>PRODUCT LENGTH/DEPTH</b>	1.85 in
<b>PRODUCT HEIGHT</b>	2.17 in
<b>PRODUCT WIDTH</b>	0.24 in
<b>PRODUCT WEIGHT</b>	0.04 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL Listed CSA Certified



Powering Business Worldwide