



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Screw Connection Fuse Terminal Blocks

**XBUT4FBE**

**UPC:**782116905218

### Dimensions:

- **Height:** 2.24 IN
- **Length:** .24 IN
- **Width:** X

### Warranties:

- 1 year

### Specifications:

- **Type:** IEC-XB Series
- **Amperage Rating:** 6.30A (IEC), 6.30A (UL)
- **Voltage Rating:** UL 600V
- **Maximum Wire Size:** 10 AWG/4 mm<sup>2</sup>
- **Quantity:** 50
- **Used With:** 5 x 20 mm Fuse
- **Wire Size:** #26-10 AWG
- **Color:** Black

### Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBUT4FBE](#)

### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data





Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Screw Connection Fuse Terminal Blocks

**XBUT4FBE**

**UPC:**782116905218

### Dimensions:

- **Height:** 2.24 IN
- **Length:** .24 IN
- **Width:** X

### Warranties:

- 1 year

### Specifications:

- **Type:** IEC-XB Series
- **Amperage Rating:** 6.30A (IEC), 6.30A (UL)
- **Voltage Rating:** UL 600V
- **Maximum Wire Size:** 10 AWG/4 mm<sup>2</sup>
- **Quantity:** 50
- **Used With:** 5 x 20 mm Fuse
- **Wire Size:** #26-10 AWG
- **Color:** Black

### Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBUT4FBE](#)

### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data

