



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



XCE4B4 7.6KW 25950BTU HTR *Crouse-Hinds*

| | |
|------------------|---|
| Catalog Number | XCE4B4 |
| Manufacturer | Crouse-Hinds |
| Description | Eaton Crouse-Hinds Series XC Electric Heater, 25, 950 Btu/HR, 7.6 KW, Steel, 20A Max., With Built-In Room Thermostat, 480 Vac |
| Weight per unit | N/A |
| Product Category | Panel & Cable Heaters |

Features

| | |
|------------|-------------------------------------|
| dimensions | 65.1300 IN X 8.1100 IN X 20.3000 IN |
|------------|-------------------------------------|

Descriptions

| | |
|------------------------|---|
| Description | 7.6KW 25950BTU HTR |
| extra long description | CRS-H XC E4 B4 EXPF ELECTRIC HEATER |
| Features | Crouse-Hinds series XC electric heaters are used for standby heat to prevent process heat loss, in areas where flammable liquids, gases or vapors are present. Applications include: petroleum refineries, gasoline storage, areas that use flammable liquids for cleaning parts in dip tanks, petrochemical plants, paint spraying areas, aircraft hangars and hydrogen fuel cell and battery storage. |
| Long Description | Eaton Crouse-Hinds series XC electric heater, 25,950 BTU/hr, 7.6 kW, Steel, 20A max., With built-in room thermostat, 480 Vac |
| Product Type | Expf Electric Heaters |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00662276105775 |
| Manufacturers Part Number | XC E4 B4 |
| UPC | 662276105775 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------|
| Category Description | FANS & HEATERS |
| Type | Electric heater |

Packaging

| | |
|-----------------|---|
| Carton | 1 |
| Weight Per each | 0 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Ind Facilities & Factories - Facility: Power Distribution and Control |
|-------------|---|