

# Specifications

## Eaton XJG64 SA

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 4" maximum conduit movement, 2" trade size



Photo is representative

### General specifications

|                      |                                                  |
|----------------------|--------------------------------------------------|
| PRODUCT NAME         | Eaton Crouse-Hinds series XJG expansion coupling |
| CATALOG NUMBER       | XJG64 SA                                         |
| UPC                  | 782274915920                                     |
| PRODUCT LENGTH/DEPTH | 8.75 in                                          |
| PRODUCT HEIGHT       | 4.38 in                                          |
| PRODUCT WIDTH        | 4.38 in                                          |
| PRODUCT WEIGHT       | 3.75 lb                                          |



### Certifications and compliances

|                     |                        |
|---------------------|------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous |
|---------------------|------------------------|

### Product specifications

|      |           |
|------|-----------|
| TYPE | Expansion |
|------|-----------|

|                       |           |
|-----------------------|-----------|
|                       | Locations |
| <b>STANDARDS TYPE</b> | NEC/CEC   |

|                               |                      |
|-------------------------------|----------------------|
| <b>CONDUIT TYPE</b>           | Rigid/IMC            |
| <b>TRADE SIZE</b>             | 2"                   |
| <b>CONDUIT MOVEMENT - MAX</b> | 4"                   |
| <b>MATERIAL</b>               | Copper-free aluminum |

## Resources

|                                      |                                                                                                                                                                                        |
|--------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>BROCHURES</b>                     | <a href="#">Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure</a>                                                                                                    |
| <b>CATALOGS</b>                      | <a href="#">Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page</a>                                                                                         |
| <b>CERTIFICATION REPORTS</b>         | <a href="#">XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification</a><br><a href="#">XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification</a> |
| <b>INSTALLATION INSTRUCTIONS</b>     | <a href="#">IF 343 - Type XJ Expansion Joints</a><br><a href="#">IF 1508 - Assembly-Free XJG</a>                                                                                       |
| <b>SPECIFICATIONS AND DATASHEETS</b> | <a href="#">Expansion and Deflection Couplings</a><br><a href="#">Eaton Specification Sheet - XJG64 SA</a>                                                                             |

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.

